

HiTemp140X2-TS

Thermal Shield for the HiTemp140X2 Data Logger Series

The HiTemp140X2-TS is a thermal shield designed for use with the HiTemp140X2 series of data loggers. This durable enclosure allows the data logger to be used in temperatures from -200 °C to +250 °C, making it ideal for peanut roasting, food processing, autoclave validation and other extreme temperature applications.

To use, simply place the HiTemp140X2 data logger in the IFC400 or IFC406 docking station (sold separately) and use the MadgeTech software to program a start method and reading interval. Place the HiTemp140X2 data logger in the HiTemp140X2-TS enclosure and the device is ready to be deployed.

The HiTemp140X2-TS is designed to have both probes entirely exposed while the data logger body is protected by the thermal shield. This allows full use of the length of the probe for applications that require internal temperature monitoring.



Features

- Withstands Temperatures between -200 °C up to +250 °C (see specification chart)
- Small Diameter: 2.85 in (72.4 mm)
- Compatible with all HiTemp140X2 loggers

Applications

- Peanut Roasting
- Food Processing
- Autoclave Validation
- Conveyor Ovens
- Dishwasher Testing

SPECIFICATIONS

Specifications are subject to change without notice. Specific warranty remedy limitations apply. Call (603) 456-2011 or go to madgetech.com for details.

Ambient Temperature	HiTemp140X2-TS	
	Exposure Time in Air (150 °C/302 °F)	Exposure Time in Liquid (150 °C/302 °F)
-200 °C (-328 °F)	12 minutes	N/A
-180 °C (-292 °F)	13 minutes	N/A
-160 °C (-256 °F)	15 minutes	N/A
-140 °C (-220 °F)	17 minutes	N/A
-120 °C (-184 °F)	19 minutes	N/A
-100 °C (-148 °F)	22 minutes	N/A
-80 °C (-112 °F)	27 minutes	N/A
-60 °C (-76 °F)	37 minutes	22 minutes
-40 °C to +140 °C (-40 °F to +284 °F)	Indefinitely	Indefinitely
+150 °C (+302 °F)	59 minutes	34 minutes
+160 °C (+320 °F)	51 minutes	29 minutes
+170 °C (+338 °F)	43 minutes	25 minutes
+180 °C (+356 °F)	37 minutes	23 minutes
+190 °C (+374 °F)	34 minutes	20 minutes
+200 °C (+392 °F)	31 minutes	18 minutes
+210 °C (+410 °F)	29 minutes	17 minutes
+220 °C (+428 °F)	27 minutes	16 minutes
+230 °C (+446 °F)	25 minutes	15 minutes
+240 °C (+464 °F)	23 minutes	14 minutes
+250 °C (+482 °F)	22 minutes	13 minutes

Operating Environment	-200 °C to +250 °C (-328 °F to +482 °F) (Time limited) 0 %RH to 100 %RH
Dimensions	2.85 in x 1.95 in x 1.55 in (72.4 mm x 49.5 mm x 39.4 mm)
Material	Enclosure: PTFE
Weight	6.7 oz (190 g) (not including data logger)
IP Rating	The Thermal Shield alone does not provide any sealing against fluid ingress. The Thermal Shield will inherit IP rating of the logger.

Disclaimer & Terms of Use

Published specifications can be used to determine maximum allowable exposure times for the HiTemp140 with Thermal Shield at different temperatures beyond the normal operating range of the logger. Both the data logger and Thermal Shield must be at ambient temperature (approximately 25 °C) before being placed in the extreme temperature environment.

Immediately following exposure to high temperature, the data logger should be removed from the thermal shield (using appropriate precautions, as it could be VERY hot) OR the data logger and shield should be placed in a water bath (approximately 25 °C) for at least 15 minutes to allow it to cool. Failing to do this may allow heat trapped in the Thermal Shield to continue to heat the data logger to potentially unsafe levels.

If your application involves a ramp up to a temperature above 140 °C and/or any complex temperature profile that isn't simply a constant temperature, please contact MadgeTech to determine whether the HiTemp140 with Thermal Shield is suitable.

Please provide MadgeTech with a detailed description of your temperature profile, including temperatures, durations, ramp times, and process media (air, steam, oil, water, etc.) If MadgeTech is unable to definitively calculate the suitability of our product for your application, we can provide a test unit outfitted with a high temperature indicator sticker. This sticker has an indicator dot which will turn black if exposed to temperatures above 143 °C. Apply the sticker to the bottom of the data logger itself (not the thermal shield), remove the battery for safety, place the data logger into the thermal shield and run the assembly through the proposed temperature program. The first indicator dot on the sticker will turn black at 143 °C. If that happens, the HiTemp140 with thermal shield is not appropriate for the application and we will work to find a solution that is.



The image shows a promotional banner for WessexPower and LS Technology. At the top center is a red and blue pill-shaped logo with 'WP' in white on a red background, 'WP+LS' in white on a blue background, and three white vertical bars of increasing height. Below this, the banner is split into two columns. The left column features the WessexPower logo (a red circle with 'WP' in white), the text 'WessexPower' in bold, 'Solutions for High-tech Instrumentation' in a smaller font, and a red pill-shaped button with the website 'www.wessexpower.co.uk'. The right column features the LS Technology logo (three blue vertical bars of increasing height), the text 'LS Technology' in bold, 'E-commerce Instrumentation' in a smaller font, and a blue pill-shaped button with the website 'www.loggershop.co.uk'. At the bottom of the banner, there is a light blue bar with the text 'Telephone +44(0)1929 459 459' on the left and 'Email sales@WPLS.co.uk' on the right.

Ordering Information

HITEMP140X2-TS	PN 900285-00	Thermal Shield for the HiTemp140X2 Data Logger Series
----------------	--------------	---